

# **Product Specification Sheet**



### 12W

VT-857 12W LED GARDEN LAMP COLORCODE: GREEN GREY BODY

Lumens 720

Beam Angle 30

Dimensions 73x255mm

GREEN SKU:7552





### **Technical Information**

Instant Start:	0-100% in
Watts:	12
Lumens:	720
On/Off Cycles:	15000
Beam Angle:	30
Unit Color:	Grey
Body Type:	Aluminium
Long life:	20.000 Hours

 LED Chip Type:
 COB

 IP Rating:
 IP65

 Dimmable:
 No

 Warranty (Years):
 2

 PF:
 >0.6

 CRI:
 >80

 Operation Temperature:
 -20 to +45°c


 Input Power:
 AC:100-240V,50/60Hz

### **Features**



Perfectly designed IP65 rated garden spike with LED











Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

## Packaging

#### **Unit Details**

 Gross Weight(GW) Kgs
 0.46

 Unit CBM
 0.001224

### Master Box Packaging

Master Box Qty (Pcs Per Carton) 50
Qty Per Pallet 1000

### Listing Details

EAN Code 3800157633529

Commodity Code 9405403990

