

# **Product Specification Sheet**



VT-7613 GU10 GARDEN LAMP, ALUMINIUM BODY -BLACK IP54

Dimensions 121x80x250mm

SKU:7563





### **Technical Information**

Holder Type: GU10

Rated Load: Max 35W

Body Type: Aluminium Body + Clear PC Diffuser

IP Rating: IP54

Dimmable: No
Warranty (Years): 3
Operation Temperature: -20? to 45?
Input Power: AC:220-240V, 50/60Hz

### **Features**

- Perfect replacement for traditional wall fittings
  - Designed with an Ingress protection of IP54
- Available body type options of Aluminium and Stainless Steel
- Suitable with GU10 base lights (Fitting only Light not included)
- Easy to Install and low maintenance
- ✓ Application: Suitable for Pathways, Stairways, Passage, Walkways etc

## Packaging

#### **Unit Details**

 Gross Weight(GW) Kgs
 0.68

 Unit CBM
 0.002691

### Master Box Packaging

Master Box Qty (Pcs Per Carton) 6

Qty Per Pallet 360

### Listing Details

EAN Code 3800157636360

Commodity Code 9405109890

