

29W

VT-12031 29W LED PANEL 1200*300mm COLORCODE:4000K HIGH LUMEN



Lumens
3480

Beam Angle
120

Dimensions
1195x295x14mm

Day White
SKU:6257

2 YEARS
WARRANTY

SENSOR
COMPATIBLE



Technical Information

Instant Start: 0-100% in 1s

Watts: 29

Lumens: 3480

Shape: Rectangle

Beam Angle: 120

Unit Color: PKW

Body Type: Aluminium + PMMA + PS

Long life: 20,000 Hours

LED Chip Type: SMD

IP Rating: IP20

Dimmable: No

Warranty (Years): 2

PF: >0.9

CRI: >80

Operation Temperature: -25 to +50°C

Input Power: AC:200-240V,50/60Hz

Sensor Compatibility: Yes

Features

- ✓ Compare with incandescent, it can save over 80% electric cost
- ✓ Contemporary & Elegant Design
- ✓ Higher Light Transmission Rate
- ✓ Easy to install - Plug and play version
- ✓ Dimmable options available
- ✓ High quality power driver ensures reliable lifetime
- ✓ Controlled Glare rating values for comfortable commercial applications
- ✓ Range of Sizes to suit different workspaces
- ✓ Instant Start - 0-100% in
- ✓ No flickering, No U.V Radiation
- ✓ No Lead or Mercury content hence Environment friendly
- ✓ Application - Office, Conference Room, Showroom, Lobby, Cabin, Kitchen etc



Note: Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty