



29W

VT-12031 29W LED PANEL 1200*300mm COLORCODE:6400K HIGH LUMEN

Lumens 3480	Beam Angle 120	Dimensions 1195x295x14mm
-----------------------	--------------------------	------------------------------------

White
SKU:6258



Technical Information

Instant Start:	0-100% in 1t1s	IP Rating:	IP20
Watts:	29	Dimmable:	No
Lumens:	3480	Warranty (Years):	2
Shape:	Rectangle	PF:	>0.9
Beam Angle:	120	CRI:	>80
Unit Color:	PKW	Operation Temperature:	-25 to +50°C
Body Type:	Aluminium + PMMA + PS	Input Power:	AC:200-240V,50/60Hz
Long life:	20,000 Hours	Sensor Compatibility:	Yes
LED Chip Type:	SMD		

Features

- ✓ Compare with incandescent, it can save over 80% electric cost
- ✓ Contemporary & Elegant Design
- ✓ Higher Light Transmission Rate
- ✓ Easy to install - Plug and play version
- ✓ Dimmable options available
- ✓ High quality power driver ensures reliable lifetime
- ✓ Controlled Glare rating values for comfortable commercial applications
- ✓ Range of Sizes to suit different workspaces
- ✓ Instant Start - 0-100% in
- ✓ No flickering, No U.V Radiation
- ✓ No Lead or Mercury content hence Environment friendly
- ✓ Application - Office, Conference Room, Showroom, Lobby, Cabin, Kitchen etc



Note: Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty