



**45W**

VT-12045 45W LED PANEL-1200\*600 COLORCODE:4000K HIGH LUMEN

Lumens <b>5400</b>	Beam Angle <b>120</b>	Dimensions <b>1195x595x14mm</b>
-----------------------	--------------------------	------------------------------------

Day White  
SKU:6332



## Technical Information

Instant Start:	0-100% in lt1s	Long life:	20,000 Hours
Output Voltage:	DC 30-42V	LED Chip Type:	SMD
Watts:	45	IP Rating:	IP20
Lumens:	5400	Dimmable:	No
Shape:	Rectangle	Warranty (Years):	2
Input Current:	0.25A	PF:	>0.9
Beam Angle:	120	CRI:	>80
Output Current:	1050mA	Operation Temperature:	-25 to +50°C
Unit Color:	White	Input Power:	AC:200-240V,50/60Hz
Body Type:	Aluminium + PMMA + PS	Sensor Compatibility:	Yes

## Features

- ✓ Compare with incandescent, it can save over 80% electric cost
- ✓ Contemporary & Elegant Design
- ✓ Higher Light Transmission Rate
- ✓ Easy to install - Plug and play version
- ✓ Dimmable options available
- ✓ High quality power driver ensures reliable lifetime
- ✓ Controlled Glare rating values for comfortable commercial applications
- ✓ Range of Sizes to suit different workspaces
- ✓ Instant Start - 0-100% in
- ✓ No flickering, No U.V Radiation
- ✓ No Lead or Mercury content hence Environment friendly
- ✓ Application - Office, Conference Room, Showroom, Lobby, Cabin, Kitchen etc



Note: Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty