



10W

VT-820 10W LED WALL LIGHT COLORCODE:3000K WHITE BODY 80CM HEIGHT

Lumens 450	Beam Angle 72	Dimensions 108x800mm
----------------------	-------------------------	--------------------------------

Warm White
 SKU:8325

2 YEARS
 WARRANTY



Technical Information

Watts:	10	IP Rating:	IP65
Lumens:	450	Dimmable:	No
On/Off Cycles:	15000	Warranty (Years):	2
Beam Angle:	72	PF:	>0.5
Unit Color:	White	CRI:	>80
Body Type:	Aluminium	Operation Temperature:	-20 to +45°C
Long life:	20,000 Hours	Input Power:	AC:100-240V,50/60Hz
LED Chip Type:	COB(CREE)		

Features

- ✓ Perfect replacement for traditional fittings as they are more flexible & efficient
- ✓ Works perfectly in extreme temperatures from -20° to 50 without any adverse effects
- ✓ Specifically designed for Outdoor use
- ✓ IP65/67 Protection Rating to ensure safety
- ✓ Used for Gardens, Outdoor Residential Areas, Walkways & Passages, Driveways, Fountains, Lawns, Entrance, Patio or Terrace and similar environments

Packaging

Unit Details

Gross Weight(GW) Kgs	2.39
Unit CBM	0.02754

Listing Details

EAN Code	3800157632362
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	4
Qty Per Pallet	60

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES