

Product Specification Sheet



12W

VT-822 12W LED WALL LIGHT COLORCODE:6400K WHITE BODY

Lumens 750

Beam Angle 140

Dimensions 130x160mm

White SKU:8336





Technical Information

Watts:	12
Lumens:	750
On/Off Cycles:	>15000
Beam Angle:	140
Unit Color:	White
Body Type:	PC
I ong life:	20 000 Hours

IP Rating:	IP65
Dimmable:	No
Warranty (Years):	2
PF:	>0.5
CRI:	>80
Operation Temperature:	-20 to +45°c
Input Power:	AC:100-240V,50/60Hz

Features

- ✓ Perfect replacement for traditional fittings as they are more flexible & efficient
- ✓ Works perfectly in extreme temperatures from -20° to 50 without any adverse effects
- Specifically designed for Outdoor use
- ✓ IP65/67 Protection Rating to ensure safety
- Used for Gardens, Outdoor Residential Areas, Walkways & Passages, Driveways, Fountains, Lawns, Entrance, Patio or Terrace and similar environments

Packaging

Unit Details

 Gross Weight(GW) Kgs
 0.487

 Unit CBM
 0.002618


Master Box Packaging

Master Box Qty (Pcs Per Carton) 20
Qty Per Pallet 400

Listing Details

 EAN Code
 3800157632478

 Commodity Code
 9405403990





OUR PRODUCTS ARE CURRENTLY SOLD IN OVER 70 COUNTRIES