

# **Product Specification Sheet**



### 12W

VT-822 12W LED WALL LIGHT COLORCODE:3000K GREY BODY

Lumens 750

Beam Angle 140

Dimensions 130x160mm

Warm White SKU:8337





# **Technical Information**

Watts:	12
Lumens:	750
Beam Angle:	140
Unit Color:	Grey
Body Type:	PC
Long life:	20,000 Hours
IP Rating:	IP65

Dimmable:	No
Warranty (Years):	2
PF:	>0.5
CRI:	>80
Operation Temperature:	-20 to +45°c
Input Power:	AC:100-240V,50/60Hz

# **Features**

- ✓ Perfect replacement for traditional fittings as they are more flexible & efficient
- ✓ Works perfectly in extreme temperatures from -20° to 50 without any adverse effects
- Specifically designed for Outdoor use
- ✓ IP65/67 Protection Rating to ensure safety
- Used for Gardens, Outdoor Residential Areas, Walkways & Passages, Driveways, Fountains, Lawns, Entrance, Patio or Terrace and similar environments

# Packaging

#### **Unit Details**

 Gross Weight(GW) Kgs
 0.482

 Unit CBM
 0.002856

## Master Box Packaging

 Master Box Qty (Pcs Per Carton)
 20

 Qtv Per Pallet
 400

### Listing Details

 EAN Code
 3800157632485

 Commodity Code
 9405403990



