



5W

VT-2165D 5W PLASTIC SPOTLIGHT COLORCODE:3000K GU10 38'D

Equivalent <b>40W</b>	Lumens <b>380</b>	Beam Angle <b>38</b>	Dimensions <b>ø50x55mm</b>
--------------------------	----------------------	-------------------------	-------------------------------

Warm White  
SKU:7428




**2** YEARS  
WARRANTY



## Technical Information

EQ-WATTS: 40	LED Chip Type: SMD
Watts: 5	IP Rating: IP20
Lumens: 380	Dimmable: Yes
Holder Type: GU10	Warranty (Years): 2
On/Off Cycles: >15000	PF: >0.5
Beam Angle: 38	CRI: >80
Body Type: Plastic	Operation Temperature: -20°C to +45°C
Energy Rating: A+	Input Power: AC:220-240V, 50Hz
Long life: 30000 Hours	



## Features

- ✓ Stable SMD technology which makes the product more reliable and longlasting
- ✓ Lasts 20000 hours, which is 20 times longer than Standard halogen spotlights
- ✓ Uses 80% less energy than Standard halogen spotlights
- ✓ Excellent Heat Radiation Efficiency
- ✓ Customized exterior for a robust body
- ✓ Non – Flickering
- ✓ Reliable IC Power Driver
- ✓ Broad Range of holders like GU10, MR16, G9, G4 and G53
- ✓ Wide Voltage Range from AC: 180 – 240V , 50/60 Hz & 12V optional
- ✓ Dimmable & Non Dimmable options
- ✓ Applications - Hotels, Bars, Commercial & Residential Lighting and Exhibition Stands etc



Note: Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

## Packaging

### Unit Details

Gross Weight(GW) Kgs	0.045
Unit CBM	0.000189

### Listing Details

EAN Code	3800157636247
Commodity Code	9405403990

### Master Box Packaging

Master Box Qty (Pcs Per Carton)	200
---------------------------------	-----

READY STOCKS IN  
**UK & EU**



Dispatch within  
**24** Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER  
**70**  
COUNTRIES