12W UK Wall Plug Adapter 12V DC, 1A

multicomp PRO



Features

- · United Kingdom Fixed AC Head
- · Level VI Efficiency
- · CE Approved

RoHS Compliant

Description

This class II 12 Watt AC/DC United Kingdom plug-in power supplies provide 12 Watts of continuous power in a compact fixed wall plug enclosure suitable for use in many general power applications.

Specifications


Input Voltage Range	90V AC to 264V AC		
Input Frequency Range	47Hz to 63Hz		
Input Current Rated	0.5A Max		
Output Voltage Rating	+12V		
Output Current Range	1A		
Output Min Current	0A		
Output Connection Type	2.1mm × 5.5mm × 12mm Centre Positive – Straight Angle		
Total Output Regulation	±5%		
Line and Load Regulation	±5%		
Ripple & Noise	200mVp-p		
Efficiency	82.96% Min		
Over Voltage Protection	25V DC Maximum		
Over Load Protection	2.5A max with Auto-Recovery Function		
Short-Circuit Protection	Short circuit protection is to be included in the construction of the adaptor. The adaptor is designed to withstand continuous current of a short circuit on the output. The adaptor will be short circuit tolerant for an indefinite period.		
Operating Temperature	0°C to +40°C		
Storage Temperature	-20°C to +60°C		
Operating Humidity	20% to 85%		
Storage Humidity	5% to 95%		
Hi-Pot	3000V AC 10mA 1min		
Leakage Current	0.25mA max		
Safety Standard	Meet T-License (BS EN60950-1)		
EMI Standard	Meet CE (EN55032)		
MTBF	50K Hours		
Size Max.	70mm (L) × 49.5mm (W) × 73.2mm (H)		
Weight	104g ±15%		
Regulator Type	Switched Mode Power Supply		


Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



12W UK Wall Plug Adapter 12V DC, 1A

multicomp PRO





Dimensions: Millimetres

Part Number Table

Description		Part Number
Wall Plug Adapter, 12W, 12V DC, 1	A, UK Plug	MP001998

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

