



VT-750 WALL LAMP -MATT BLACK (DOWN)

Dimensions
208x360x170mm

SKU:7068

2 YEARS
WARRANTY



Technical Information

Holder Type: **E27**

IP Rating: **IP44**

Rated Load: **Max 40W**

Dimmable: **No**

Unit Color: **MATT BLACK**

Warranty (Years): **2**

Body Type: **Aluminium + Glass**

Input Power: **AC:220-240V,50Hz**

Features

- ✓ Traditional Garden Lamps designed to fit the Modern day requirements
- ✓ Available in different designs, shapes and sizes
- ✓ Waterproof Lamps available in series of IP rating from IP44 to IP54
- ✓ Easy to Install and low Maintenance
- ✓ Suitable with E27 base lights(Fitting only - Light not included)
- ✓ Application: Suitable for Garden, Floor, Ceiling etc

Packaging

Unit Details

Gross Weight(GW) Kgs	0.97
Length(Box)mm	215
Width(Box)mm	165
Height(Box)mm	245
Unit CBM	0.008036

Listing Details

EAN Code	3800157616218
Commodity Code	9405109890

Master Box Packaging

Master Box Qty (Pcs Per Carton)	10
Qty Per Pallet	160

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES