



VT-750 WALL LAMP -MATT WHITE(DOWN)

Dimensions  
**208x360x170mm**

SKU:7069

**2 YEARS**  
WARRANTY



## Technical Information

Holder Type: **E27**

IP Rating: **IP44**

Rated Load: **Max 40W**

Dimmable: **No**

Unit Color: **MATT WHITE**

Warranty (Years): **2**

Body Type: **Aluminium + Glass**

Input Power: **AC:220-240V,50Hz**

## Features

- ✓ Traditional Garden Lamps designed to fit the Modern day requirements
- ✓ Available in different designs, shapes and sizes
- ✓ Waterproof Lamps available in series of IP rating from IP44 to IP54
- ✓ Easy to Install and low Maintenance
- ✓ Suitable with E27 base lights(Fitting only - Light not included)
- ✓ Application: Suitable for Garden, Floor, Ceiling etc

## Packaging

### Unit Details

Gross Weight(GW) Kgs	0.97
Length(Box)mm	215
Width(Box)mm	165
Height(Box)mm	245
Unit CBM	0.008036

### Listing Details

EAN Code	3800157616225
Commodity Code	9405109890

### Master Box Packaging

Master Box Qty (Pcs Per Carton)	10
Qty Per Pallet	160

READY STOCKS IN  
**UK & EU**



Dispatch within  
24 Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER  
**70**  
COUNTRIES