

Product Specification Sheet



VT-754 WALL LAMP-MATT BLACK(FROST GLASS)

Dimensions 245x180x93mm

SKU:7076





Technical Information

Holder Type: E27

Rated Load: Max 40W

Unit Color: Matt Black

Body Type: Aluminium + Glass

IP Rating: IP44

Dimmable: No

Warranty (Years): 3

Input Power: AC:220-240V,50Hz

Features

- Traditional Garden Lamps designed to fit the Modern day requirements
 - Available in different designs, shapes and sizes
- Waterproof Lamps available in series of IP rating from IP44 to IP54
- Easy to Install and low Maintenance
- Suitable with E27 base lights(Fitting only Light not included)
- Application: Suitable for Garden, Floor, Ceiling etc.

Packaging

Unit Details

Gross Weight(GW) Kgs	1.53
Length(Box)mm	185
Width(Box)mm	100
Height(Box)mm	250
Unit CBM	0.0045
Mantau Dan Bankania	

Master Box Packaging

Master Box Qty (Pcs Per Carton)	10
Qty Per Pallet	250

Listing Details

EAN Code	3800157616294
Commodity Code	9405109890

