

Product Specification Sheet



6W

VT-756 6W-WALL LAMP WITH BRIDGELUX CHIP COLORCODE:3000k BLACK ROUND

Lumens 660

Beam Angle 120

Dimensions 140x115x100mm

Warm White SKU:7081







Technical Information

Instant Start:	0-100% in lt1s
Watts:	6
Lumens:	660
Shape:	Round
Beam Angle:	120
Unit Color:	Black
Body Type:	Aluminium
Long life:	20 000 Hours

IP Rating:	IP65
Dimmable:	No
Warranty (Years):	2
PF:	>0.45
CRI:	>80
Operation Temperature:	-25 to +50°c
Input Power:	AC:220-240V,50/60Hz
Sensor Compatibility:	Yes

Features



High Quality Bridgelux chips for reliable operation and lifetime

Get range of up-down beams with Adjustable beam angle to feel range of aesthetics

Constructed to high quality aluminum for efficient heat dissipation

Cylindrical & Cubical fixtures in 3 colors to fit into range of archetictural structures

Elegant replacement for traditional up-down lighting

Application: Perfect for living rooms, pathways, balconies, facades etc





Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	0.82
Length(Box)mm	115
Width(Box)mm	120
Height(Box)mm	110
Unit CBM	0.00198
Master Box Packaging	

Master Box Qty (Pcs Per Carton)	20
Qty Per Pallet	380

Listing Details

EAN Code	3800157616409
Commodity Code	9405403990

