

Product Specification Sheet



Technical Information

er Type:	GU10	Dimmable:	No
ated Load:	Max 35W	Warranty (Years):	2
Jnit Color:	STAINLESS STEEL	Operation Temperature:	-25 to +50°c
ody Type:	Stainless Steel	Input Power:	AC:220-240V,50Hz
P Rating:	IP44		

Features

- Perfect replacement for traditional wall fittings
- Designed with Ingress protection of IP44
- Available body type options of Aluminium and Stainless Steel
- Suitable with GU10 base lights (Fitting only Light not included)
- Easy to Install and low Maintenance
- Application: Suitable for Pathways, Stairways, Passage, Walkways etc

Packaging

Unit Details		Listing Details	
Gross Weight(GW) Kgs	0.5	EAN Code	3800157617642
Unit CBM	0.001176	Commodity Code	9405109890
Master Box Packaging			
Master Box Qty (Pcs Per Carton)	24		
Qty Per Pallet	864		

