



VT-7642 SLEEK GU10 WALL FITTING, STAINLESS STEEL BODY- 2 WAY
IP44

Dimensions
105x76x207mm

SKU:7507

2 YEARS
WARRANTY



Technical Information

Holder Type: 2XGU10

Rated Load: Max 2x35W

Unit Color: STAINLESS STEEL

Body Type: Stainless Steel

IP Rating: IP44

Dimmable: No

Warranty (Years): 2

Operation Temperature: -25 to +50°C

Input Power: AC:220-240V,50Hz

Features

- ✓ Perfect replacement for traditional wall fittings
- ✓ Designed with Ingress protection of IP44
- ✓ Available body type options of Aluminium and Stainless Steel
- ✓ Suitable with GU10 base lights (Fitting only - Light not included)
- ✓ Easy to Install and low Maintenance
- ✓ Application: Suitable for Pathways, Stairways, Passage, Walkways etc

Packaging

Unit Details

Gross Weight(GW) Kgs	0.585
Unit CBM	0.002244

Listing Details

EAN Code	3800157617666
Commodity Code	9405109890

Master Box Packaging

Master Box Qty (Pcs Per Carton)	16
Qty Per Pallet	384

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER

70

COUNTRIES