

Product Specification Sheet



VT-7651 SLEEK GU10 WALL FITTING(ALUMINUM)SQUARE-BLACK 1 WAY IP44

Dimensions 92x68x80mm

SKU:7510





Technical Information

Holder Type:	GU10
Shape:	Square
Rated Load:	Max 35W
Unit Color:	Black
Body Type:	Aluminium

IP Rating: IP44

Dimmable: No

Warranty (Years): 2

Operation Temperature: -25 to +50°c

Input Power: AC:220-240V,50Hz

Features

- Perfect replacement for traditional wall fittings
- Designed with Ingress protection of IP44
- Available body type options of Aluminium and Stainless Steel
- ✓ Suitable with GU10 base lights (Fitting only Light not included)
- Easy to Install and low Maintenance
- ✓ Application: Suitable for Pathways, Stairways, Passage, Walkways etc

Packaging

Unit Details

 Gross Weight(GW) Kgs
 0.39

 Unit CBM
 0.000756

Master Box Packaging

 Master Box Qty (Pcs Per Carton)
 24

 Qty Per Pallet
 1536

Listing Details

 EAN Code
 3800157617697

 Commodity Code
 9405109890

