

# **Product Specification Sheet**



VT-7662 GU10 WALL FITTING SQUARE,SS BODY WITH BORDER-BLACK 2 WAY IP44

Dimensions 85x87x250mm

SKU:7512





### **Technical Information**

Holder Type: 2XGU10

Shape: Square

Rated Load: Max 2x11W

Unit Color: Black

Body Type: Stainless Steel

IP Rating: IP44

Dimmable: No

Warranty (Years): 2

Operation Temperature: -25 to +50°c

Input Power: AC:220-240V,50Hz

#### **Features**

- Perfect replacement for traditional wall fittings
- Designed with Ingress protection of IP44
- Available body type options of Aluminium and Stainless Steel
- Suitable with GU10 base lights (Fitting only Light not included)
- Easy to Install and low Maintenance
- ✓ Application: Suitable for Pathways, Stairways, Passage, Walkways etc

## Packaging

**Unit Details** 

 Gross Weight(GW) Kgs
 0.965

 Unit CBM
 0.0023465

Master Box Packaging

Master Box Qty (Pcs Per Carton)

#### Listing Details

EAN Code 3800157617710

Commodity Code 9405109890



12

OUR PRODUCTS ARE CURRENTLY SOLD IN OVER 70 COUNTRIES