

## **Product Specification Sheet**



Technical Information							
Holder Type:	E27		IP Rating:	IP44			
Rated Load:	Max 60W		Dimmable:	No			
Unit Color:	MATT BLACK		Warranty (Years):	2			
Body Type:	Aluminium + Glass		Input Power:	AC:220-240V			

## Features

- / Traditional Garden Lamps designed to fit the Modern day requirements
- Available in different designs, shapes and sizes
- Waterproof Lamps available in series of IP rating from IP44 to IP54
- / Easy to Install and low Maintenance
- Suitable with E27 base lights(Fitting only Light not included)
- Application: Suitable for Garden, Floor, Ceiling etc

## Packaging

Unit Details		Listing Details	
Gross Weight(GW) Kgs	1.108	EAN Code	3800157617789
Unit CBM	0.009016	Commodity Code	9405109890
Master Box Packaging			
Master Box Qty (Pcs Per Carton)	12		
Qty Per Pallet	144		

