



VT-760 WALL LAMP SMALL-MATT WHITE(UP)

Dimensions
225x400x148mm

SKU:7520

2 YEARS
WARRANTY



Technical Information

Holder Type: **E27**

Rated Load: **Max 60W**

Unit Color: **MATT WHITE**

Body Type: **Aluminium + Glass**

IP Rating: **IP44**

Dimmable: **No**

Warranty (Years): **2**

Input Power: **AC:220-240V**

Features

- ✓ Traditional Garden Lamps designed to fit the Modern day requirements
- ✓ Available in different designs, shapes and sizes
- ✓ Waterproof Lamps available in series of IP rating from IP44 to IP54
- ✓ Easy to Install and low Maintenance
- ✓ Suitable with E27 base lights(Fitting only - Light not included)
- ✓ Application: Suitable for Garden, Floor, Ceiling etc

Packaging

Unit Details

Gross Weight(GW) Kgs	1.125
Unit CBM	0.009016

Listing Details

EAN Code	3800157617796
Commodity Code	9405109890

Master Box Packaging

Master Box Qty (Pcs Per Carton)	12
Qty Per Pallet	144

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER

70

COUNTRIES