



VT-761 WALL LAMP LARGE-MATT WHITE(UP)

Dimensions  
**245x445x185mm**

SKU:7522

**2 YEARS**  
WARRANTY



## Technical Information

Holder Type: **E27**

Rated Load: **Max 60W**

Unit Color: **MATT WHITE**

Body Type: **Aluminium + Glass**

IP Rating: **IP44**

Dimmable: **No**

Warranty (Years): **2**

Input Power: **AC:220-240V**

## Features

- ✓ Traditional Garden Lamps designed to fit the Modern day requirements
- ✓ Available in different designs, shapes and sizes
- ✓ Waterproof Lamps available in series of IP rating from IP44 to IP54
- ✓ Easy to Install and low Maintenance
- ✓ Suitable with E27 base lights(Fitting only - Light not included)
- ✓ Application: Suitable for Garden, Floor, Ceiling etc

# Packaging

## Unit Details

|                      |          |
|----------------------|----------|
| Gross Weight(GW) Kgs | 1.5      |
| Unit CBM             | 0.014725 |

## Listing Details

|                |               |
|----------------|---------------|
| EAN Code       | 3800157617819 |
| Commodity Code | 9405109890    |

## Master Box Packaging

|                                 |    |
|---------------------------------|----|
| Master Box Qty (Pcs Per Carton) | 8  |
| Qty Per Pallet                  | 96 |

READY STOCKS IN  
**UK & EU**



Dispatch within  
**24** Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER

**70**

COUNTRIES