



VT-852 WALL LAMP(1\*E27) WITH CLEAR PC COVER -DOWN

Dimensions  
**290x250x525mm**

SKU:7531

**3 YEARS**  
WARRANTY



## Technical Information

Holder Type: **E27**

Rated Load: **Max 60W**

Unit Color: **Matt Black**

Body Type: **Aluminium Lampbody + Glass**

IP Rating: **IP44**

Dimmable: **No**

Warranty (Years): **3**

Input Power: **AC:220-240V,50Hz**

## Features

- ✓ Traditional Garden Lamps designed to fit the Modern day requirements
- ✓ Available in different designs, shapes and sizes
- ✓ Waterproof Lamps available in series of IP rating from IP44 to IP54
- ✓ Easy to Install and low Maintenance
- ✓ Suitable with E27 base lights(Fitting only - Light not included)
- ✓ Application: Suitable for Garden, Floor, Ceiling etc

## Packaging

### Unit Details

Gross Weight(GW) Kgs	1.285
Unit CBM	0.0234

### Listing Details

EAN Code	3800157630078
Commodity Code	9405109890

### Master Box Packaging

Master Box Qty (Pcs Per Carton)	6
Qty Per Pallet	24

READY STOCKS IN  
**UK & EU**



Dispatch within  
**24** Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER

**70**

COUNTRIES