

Product Specification Sheet



VT-853 WALL LAMP(1*E27) WITH CLEAR PC COVER-UP

Dimensions 290x250x525mm

SKU:7532





Technical Information

Holder Type: E27

Rated Load: Max 60W

Unit Color: Matt Black

Body Type: Aluminium Lampbody + Glass

IP Rating: IP44

Dimmable: No

Warranty (Years): 3

Input Power: AC:220-240V,50Hz

Features

- Traditional Garden Lamps designed to fit the Modern day requirements
 - Available in different designs, shapes and sizes
- Waterproof Lamps available in series of IP rating from IP44 to IP54
- Easy to Install and low Maintenance
- Suitable with E27 base lights(Fitting only Light not included)
- ✓ Application: Suitable for Garden, Floor, Ceiling etc

Packaging

Unit Details

 Gross Weight(GW) Kgs
 1.335

 Unit CBM
 0.0341

Master Box Packaging

Master Box Qty (Pcs Per Carton) 6
Qty Per Pallet 42

Listing Details

 EAN Code
 3800157630085

 Commodity Code
 9405109890

