

# **Product Specification Sheet**



### **Technical Information**

Holder Type: GU10 IP Rating: IP44

Shape: Round Dimmable: No

Rated Load: Max 35W Warranty (Years): 2

Unit Color: White Input Power: AC:220-240V,50Hz

Body Type: Aluminium

### **Features**

- ✓ Perfect replacement for traditional wall fittings
- Designed with Ingress protection of IP44
- ✓ Available body options of Aluminium and Stainless Steel
- ✓ Suitable with GU10 base lights (Fitting only Light not included)
- Easy to Install and low Maintenance
- ✓ Application: Suitable for Pathways, Stairways, Passage, Walkways etc

## Packaging

#### **Unit Details**

 Gross Weight(GW) Kgs
 0.38

 Unit CBM
 0.00081

### Master Box Packaging

 Master Box Qty (Pcs Per Carton)
 24

 Qty Per Pallet
 1344

### **Listing Details**

 EAN Code
 3800157630719

 Commodity Code
 9405109890

