

Product Specification Sheet



VT-7662 GU10 WALL FITTING SQUARE,SS BODY WITH BORDER-WHITE BODY,2 WAY IP44

Dimensions 85x87x250mm

SKU:7543





Technical Information

Holder Type: 2XGU10

Shape: Square

Rated Load: Max 2x11W

Unit Color: White

Body Type: Stainless Steel

IP Rating: IP44

Dimmable: No

Warranty (Years): 3

Input Power: AC:220-240V,50Hz

Features

- Perfect replacement for traditional wall fittings
- Designed with Ingress protection of IP44
- ✓ Available body options of Aluminium and Stainless Steel
- ✓ Suitable with GU10 base lights (Fitting only Light not included)
- Easy to Install and low Maintenance
- ✓ Application: Suitable for Pathways, Stairways, Passage, Walkways etc

Packaging

Unit Details

Gross Weight(GW) Kgs 0.94
Unit CBM 0.0026

Master Box Packaging

 Master Box Qty (Pcs Per Carton)
 12

 Qty Per Pallet
 480

Listing Details

 EAN Code
 3800157630740

 Commodity Code
 9405109890

