

# **Product Specification Sheet**



VT-7611 ADJUSTABLE HEAD GU10 WALL FITTING(ALUMINUM) 1 WAY IP44

Dimensions 100x66x92mm

SKU:7553





### **Technical Information**

Holder Type: GU10

Rated Load: MAX 35W

Body Type: Aluminium

IP Rating: IP44

Dimmable: No Warranty (Years): 3

Input Power: AC:220-240V,50Hz

### **Features**

- Perfect replacement for traditional wall fittings
- Designed with Ingress protection of IP44
- Available body options of Aluminium and Stainless Steel
- Suitable with GU10 base lights (Fitting only Light not included)
- Easy to Install and low Maintenance
- Application: Suitable for Pathways, Stairways, Passage, Walkways etc

## Packaging

#### **Unit Details**

0.528 Gross Weight(GW) Kgs Unit CBM 0.000968

### Master Box Packaging

Master Box Qty (Pcs Per Carton) 24 Qty Per Pallet 1152

### Listing Details

EAN Code 3800157633574 Commodity Code 9405109890



www.vtacexports.com

COUNTRIES