



VT-7622 GU10 WALL FITTING, STAINLESS STEEL BODY, 2 WAY
 IP44-MATT WHITE

Dimensions
93x85x163mm

SKU:7570

2 YEARS
 WARRANTY

SENSOR
 COMPATIBLE



Technical Information

Holder Type: GU10	Dimmable: No
Rated Load: Max 2x35W	Warranty (Years): 2
Unit Color: Matt White	Operation Temperature: -20°C to +45°C
Body Type: Stainless Steel	Input Power: AC:220-240V,50Hz
IP Rating: IP44	Sensor Compatibility: Yes

Features

- ✓ Perfect replacement for traditional wall fittings
- ✓ Designed with Ingress protection of IP44
- ✓ Available body type options of Aluminium and Stainless Steel
- ✓ Suitable with GU10 base lights (Fitting only - Light not included)
- ✓ Easy to Install and low Maintenance
- ✓ Application: Suitable for Pathways, Stairways, Passage, Walkways etc

Packaging

Unit Details

Gross Weight(GW) Kgs	0.720625
Unit CBM	0.002167

Listing Details

EAN Code	3800157640442
Commodity Code	9405109890

Master Box Packaging

Master Box Qty (Pcs Per Carton)	16
Qty Per Pallet	560

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES