


Product Specification Sheet



4W

VT-706 4W LED WALL LIGHT COLORCODE:4000K IP65 BLACK BODY ROUND

Lumens 440

Beam Angle 360

Dimensions 150x50mm

Day White SKU:8216







Technical Information

Instant Start:	0-100% in lt1s
Watts:	4
Lumens:	440
Shape:	Round
Beam Angle:	360
Unit Color:	Black
Body Type:	Aluminium + Acrylic
Long life:	20.000 Hours

IP Rating:	IP65
Dimmable:	No
Warranty (Years):	2
PF:	>0.5
CRI:	>80
Operation Temperature:	-25 to +50°c
Input Power:	AC:220-240V,50/60Hz
Sensor Compatibility:	Yes

Features

ž

Perfect choice for Interior and Exterior aesthetics

Wall washer to create attractive beam designs

High quality LED Chips for reliable lighting effect

IP65 rated solid ingress protection

Glass screen for controlled light beams

Available in different color options - Warm White and Day White

Applications - Outdoor, Façade, Residential, Restaurants, Building and many more





Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	0.69
Length(Box)mm	160
Width(Box)mm	180
Height(Box)mm	55
Unit CBM	0.001584
Master Box Packaging	

Master Box Packaging

Master Box Qty (Pcs Per Carton)	20
Qty Per Pallet	720

Listing Details

EAN Code	3800157623339
Commodity Code	9405403990

