


Product Specification Sheet



7W VT-707 7W LED WALL LIGHT COLORCODE:4000K IP65 WHITE BODY

Lumens 770

Beam Angle 360

Dimensions 110x120x170mm

Day White SKU:8218







Technical Information

Instant Start:	0-100% in lt1s
Watts:	7
Lumens:	770
Beam Angle:	360
Unit Color:	White
Body Type:	Aluminium
Long life:	20,000 Hours
IP Rating:	IP65

Dimmable:	No
Warranty (Years):	2
PF:	>0.5
CRI:	>80
Operation Temperature:	-25 to +50°c
Input Power:	AC:220-240V,50/60Hz
Sensor Compatibility:	Yes

Features



Perfect choice for in-line lighting with Architectural structures

4 way wall washer to create blade lighting effects

Create your light show in facades, corridors, stage shows etc

High quality LED chips for a reliable lighting effect

Efficient LED Driver & intruded heat sink for reliable lifespan

Reflective PMMA Screen for 360 degree light ray transmission

IP65 rated solid ingress protection

Applications - Outdoor, Façade, Residential, Restaurants, Building and many more



Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	0.921
Length(Box)mm	160
Width(Box)mm	130
Height(Box)mm	130
Unit CBM	0.002704
Master Box Packaging	

Master Box Qty (Pcs Per Carton)	20
Qty Per Pallet	300

Listing Details

EAN Code	3800157623353
Commodity Code	9405403990

