

Product Specification Sheet



9W VT-710 9W LED WALL LIGHT COLORCODE:3000K IP20 BLACK BODY

Lumens 990 Beam Angle 360

Dimensions 210x80mm

Warm White SKU:8227







Technical Information

Instant Start:	0-100% in lt1s
Watts:	9
Lumens:	990
Beam Angle:	360
Unit Color:	Black
Body Type:	Aluminium + Acrylic
Long life:	20,000 Hours
IP Rating:	IP20

 Dimmable:
 No

 Warranty (Years):
 2

 PF:
 >0.5

 CRI:
 >80

 Operation Temperature:
 -25 to +50°c

 Input Power:
 AC:220-240V,50/60Hz

 Sensor Compatibility:
 Yes

Features



Perfect choice of Interior lightingin for fabulous aesthetics and appeal





Portability and ease of maintenance

Available in different color options - Warm White and Day White

Applications - Residential, Building, Restaurants, Décor etc





Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	0.8
Length(Box)mm	220
Width(Box)mm	220
Height(Box)mm	100
Unit CBM	0.00484
Master Box Packaging	

Master Box Qty (Pcs Per Carton)	20
Qtv Per Pallet	320

Listing Details

EAN Code	3800157623445
Commodity Code	9405403990

