



9W

VT-8056 9W LED UP/DOWN OUTDOOR SOFT LIGHT-MEDIUM
 COLORCODE:6400K GREY BODY


Lumens 400	Beam Angle 90	Dimensions 173x81x46mm
----------------------	-------------------------	----------------------------------

White
 SKU:8241



Technical Information

Instant Start:	0-100% in lt1s	IP Rating:	IP65
Watts:	9	Dimmable:	No
Lumens:	400	Warranty (Years):	2
Beam Angle:	90	PF:	>0.9
Unit Color:	Grey	CRI:	>80
Body Type:	PC	Operation Temperature:	-20 to +45°c
Long life:	30,000 Hours	Input Power:	AC:100-240V,50/60Hz
LED Chip Type:	SMD2835	Sensor Compatibility:	Yes



Features

- ✓ Perfect Soft lighting option for your Landscape,Garden & Patios
- ✓ Splendid designs made of high endurance PC material
- ✓ High quality PC material for Diffused and Controlled light output
- ✓ IP65 rated solid ingress protection
- ✓ Applications - Outdoor, Façade, Residential, Restaurants, Building and many more



Note: Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	0.358
Length(Box)mm	180
Width(Box)mm	90
Height(Box)mm	55
Unit CBM	0.000891

Listing Details

EAN Code	3800157625814
Commodity Code	9405403990



Master Box Packaging

Master Box Qty (Pcs Per Carton)	20
Qty Per Pallet	1440

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES