

# **Product Specification Sheet**



### 18W VT-818 18W LED WALL LAMP COLORCODE:3000K WHITE

Lumens 1440 Beam Angle 100

Dimensions 605x100x93mm

Warm White SKU:8258







## **Technical Information**


Instant Start:	0-100% in lt1s
Watts:	18
Lumens:	1440
Beam Angle:	100
Unit Color:	White
Body Type:	Plastic + Metal
Long life:	30,000 Hours
LED Chip Type:	SMD


IP Rating:	IP20
Dimmable:	No
Warranty (Years):	3
PF:	>0.5
CRI:	>80
Operation Temperature:	-20 to +45°c
Input Power:	AC 220-240V, 50/60Hz
Sensor Compatibility:	Yes

### **Features**



Perfect choice of Interior lightingin for fabulous aesthetics and appeal





Portability and ease of maintenance

Available in different color options - Warm White and Day White

Applications - Residential, Building, Restaurants, Décor etc





Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

# Packaging

### **Unit Details**

Gross Weight(GW) Kgs	0.992
Length(Box)mm	120
Width(Box)mm	610
Height(Box)mm	110
Unit CBM	0.008052
Master Boy Packaging	

#### Master Box Packaging

Master Box Qty (Pcs Per Carton)	12
Qty Per Pallet	192

## Listing Details

EAN Code	3800157627085
Commodity Code	9405403990

