

18W

VT-818 18W LED WALL LAMP COLORCODE:4000K BLACK



Lumens
1440

Beam Angle
100

Dimensions
605x100x93mm

Day White
SKU:8261

3 YEARS
WARRANTY

SENSOR
COMPATIBLE



Technical Information

Instant Start: 0-100% in 1s

Watts: 18

Lumens: 1440

Beam Angle: 100

Unit Color: Black

Body Type: Plastic + Metal

Long life: 30,000 Hours

LED Chip Type: SMD

IP Rating: IP20

Dimmable: No

Warranty (Years): 3

PF: >0.5

CRI: >80

Operation Temperature: -20 to +45°C

Input Power: AC 220-240V, 50/60Hz

Sensor Compatibility: Yes

Features

- ✓ Perfect choice of Interior lighting for fabulous aesthetics and appeal
- ✓ High quality LED chips for a reliable lighting effect
- ✓ Efficient LED Driver & intruded heat sink for reliable lifespan
- ✓ Portability and ease of maintenance
- ✓ Available in different color options - Warm White and Day White
- ✓ Applications - Residential, Building, Restaurants, Décor etc

Note:



Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	0.992
Length(Box)mm	120
Width(Box)mm	610
Height(Box)mm	110
Unit CBM	0.008052

Listing Details

EAN Code	3800157627115
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	12
Qty Per Pallet	192

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES