

Product Specification Sheet



4.50W

VT-805 4.5W LED WALL LAMP COLORCODE:3000K WHITE

Lumens 360

Beam Angle 100

Dimensions 100x94x45mm

Warm White SKU:8262







Technical Information

Instant Start:	0-100% in lt1s
Watts:	4.5000
Lumens:	360
Beam Angle:	100
Unit Color:	White
Body Type:	Plastic + Metal
Long life:	30,000 Hours
LED Chip Type:	SMD

IP Rating:	IP20
Dimmable:	No
Warranty (Years):	3
PF:	>0.5
CRI:	>80
Operation Temperature:	-20 to +45°c
Input Power:	AC 220-240V, 50/60Hz
Sensor Compatibility:	Yes

Features



Perfect choice of Interior lightingin for fabulous aesthetics and appeal





Efficient LED Driver & intruded heat sink for reliable lifespan

Portability and ease of maintenance

Available in different color options - Warm White and Day White

Applications - Residential, Building, Restaurants, Décor etc



Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	0.338
Length(Box)mm	125
Width(Box)mm	110
Height(Box)mm	80
Unit CBM	0.0011

Master Box Packaging

Master Box Qty (Pcs Per Carton)	12
Qty Per Pallet	864

Listing Details

EAN Code	3800157627122
Commodity Code	9405403990

