



**4.50W**

VT-805 4.5W LED WALL LAMP COLORCODE:4000K WHITE

Lumens <b>360</b>	Beam Angle <b>100</b>	Dimensions <b>100x94x45mm</b>
----------------------	--------------------------	----------------------------------

Day White  
SKU:8264

**3 YEARS**  
WARRANTY

**SENSOR**  
COMPATIBLE




## Technical Information

Instant Start:	0-100% in lt1s	IP Rating:	IP20
Watts:	4.5000	Dimmable:	No
Lumens:	360	Warranty (Years):	3
Beam Angle:	100	PF:	>0.5
Unit Color:	White	CRI:	>80
Body Type:	Plastic + Metal	Operation Temperature:	-20 to +45°C
Long life:	30,000 Hours	Input Power:	AC 220-240V, 50/60Hz
LED Chip Type:	SMD	Sensor Compatibility:	Yes

## Features

- ✓ Perfect choice of Interior lightingin for fabulous aesthetics and appeal
- ✓ High quality LED chips for a reliable lighting effect
- ✓ Efficient LED Driver & intruded heat sink for reliable lifespan
- ✓ Portability and ease of maintenance
- ✓ Available in different color options - Warm White and Day White
- ✓ Applications - Residential, Building, Restaurants, Décor etc

Note:  Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

# Packaging

## Unit Details

Gross Weight(GW) Kgs	0.338
Length(Box)mm	125
Width(Box)mm	110
Height(Box)mm	80
Unit CBM	0.0011

## Listing Details

EAN Code	3800157627146
Commodity Code	9405403990

## Master Box Packaging

Master Box Qty (Pcs Per Carton)	12
Qty Per Pallet	864

READY STOCKS IN  
**UK & EU**



Dispatch within  
24 Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER  
**70**  
COUNTRIES