

# **Product Specification Sheet**



### 9W VT-810 9W LED WALL LAMP COLORCODE:3000K WHITE

Lumens 720

Beam Angle 100

Dimensions 400x100x94mm

Warm White SKU:8266







# **Technical Information**

| Instant Start: | 0-100% in lt1s  |
|----------------|-----------------|
| Watts:         | 9               |
| Lumens:        | 720             |
| Beam Angle:    | 100             |
| Unit Color:    | White           |
| Body Type:     | Plastic + Metal |
| Long life:     | 30,000 Hours    |
| LED Chip Type: | SMD             |

| IP Rating:             | IP20                 |
|------------------------|----------------------|
| Dimmable:              | No                   |
| Warranty (Years):      | 3                    |
| PF:                    | >0.5                 |
| CRI:                   | >80                  |
| Operation Temperature: | -20 to +45°c         |
| Input Power:           | AC 220-240V, 50/60Hz |
| Sensor Compatibility:  | Yes                  |
|                        |                      |

### **Features**



Perfect choice of Interior lightingin for fabulous aesthetics and appeal



Efficient LED Driver & intruded heat sink for reliable lifespan

Portability and ease of maintenance

Available in different color options - Warm White and Day White

Applications - Residential, Building, Restaurants, Décor etc



Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

# Packaging

#### **Unit Details**

| Gross Weight(GW) Kgs | 0.612  |
|----------------------|--------|
| Length(Box)mm        | 110    |
| Width(Box)mm         | 400    |
| Height(Box)mm        | 100    |
| Unit CBM             | 0.0044 |
|                      |        |

### Master Box Packaging

| Master Box Qty (Pcs Per Carton) | 12  |
|---------------------------------|-----|
| Qty Per Pallet                  | 240 |

# Listing Details

| EAN Code       | 3800157627160 |
|----------------|---------------|
| Commodity Code | 9405403990    |

