

Product Specification Sheet



9W VT-810 9W LED WALL LAMP COLORCODE:4000K WHITE

Lumens 720

Beam Angle 100

Dimensions 400x100x94mm

Day White SKU:8268







Technical Information

| Instant Start: | 0-100% in lt1s |
|----------------|-----------------|
| Watts: | 9 |
| Lumens: | 720 |
| Beam Angle: | 100 |
| Unit Color: | White |
| Body Type: | Plastic + Metal |
| Long life: | 30,000 Hours |
| LED Chip Type: | SMD |

| IP Rating: | IP20 |
|------------------------|----------------------|
| Dimmable: | No |
| Warranty (Years): | 3 |
| PF: | >0.5 |
| CRI: | >80 |
| Operation Temperature: | -20 to +45°c |
| Input Power: | AC 220-240V, 50/60Hz |
| Sensor Compatibility: | Yes |
| | |

Features



Perfect choice of Interior lightingin for fabulous aesthetics and appeal



Efficient LED Driver & intruded heat sink for reliable lifespan

Portability and ease of maintenance

Available in different color options - Warm White and Day White

Applications - Residential, Building, Restaurants, Décor etc



Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

| Gross Weight(GW) Kgs | 0.612 |
|----------------------|--------|
| Length(Box)mm | 110 |
| Width(Box)mm | 400 |
| Height(Box)mm | 100 |
| Unit CBM | 0.0044 |
| | |

Master Box Packaging

| Master Box Qty (Pcs Per Carton) | 12 |
|---------------------------------|-----|
| Qty Per Pallet | 240 |

Listing Details

| EAN Code | 3800157627184 |
|----------------|---------------|
| Commodity Code | 9405403990 |

