



5W

VT-825 5W LED WALL LIGHT COLORCODE:3000K -WHITE BODY

Lumens 550	Beam Angle 120	Dimensions 170x170x75mm
----------------------	--------------------------	-----------------------------------

Warm White
 SKU:8280

2 YEARS
 WARRANTY

SENSOR
 COMPATIBLE



Technical Information

Watts:	5	Dimmable:	No
Lumens:	550	Warranty (Years):	2
Beam Angle:	120	PF:	>0.5
Unit Color:	White	CRI:	>80
Body Type:	Aluminium	Operation Temperature:	-20°C to +45°C
Long life:	20,000 Hours	Input Power:	AC:220-240V,50/60Hz
LED Chip Type:	SMD	Sensor Compatibility:	Yes
IP Rating:	IP65		

Features

- ✓ Modern Wall lights available in sleek and stylish designs.
- ✓ Excellent heat dissipation
- ✓ Available in different color options - Warm White and Day White
- ✓ Easy installation and Maintenance
- ✓ Application: Perfect for halls, pathways, Bedroom, Kitchen etc



Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	0.67
Unit CBM	0.004

Listing Details

EAN Code	3800157629744
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	20
Qty Per Pallet	360

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER

70

COUNTRIES