

Product Specification Sheet



5W

VT-825 5W LED WALL LIGHT COLORCODE:4000K -GREY BODY

Lumens 550

Beam Angle 120

Dimensions 170x170x75mm

Day White SKU:8285







Technical Information

Watts:	5
Lumens:	550
Beam Angle:	120
Unit Color:	Grey
Body Type:	Aluminium
Long life:	20,000 Hours
LED Chip Type:	SMD
IP Rating:	IP65

Dimmable: Warranty (Years): PF: >0.5 >80 Operation Temperature: -20°C to +45°C AC:220-240V,50/60Hz Input Power: Sensor Compatibility:

Features



Modern Wall lights available in sleek and stylish designs.



Excellent heat dissipation



Available in different color options - Warm White and Day White



Easy installation and Maintenance



Application: Perfect for halls, pathways, Bedroom, Kitchen etc





Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

 Gross Weight(GW) Kgs
 0.67

 Unit CBM
 0.004

Master Box Packaging

 Master Box Qty (Pcs Per Carton)
 20

 Qty Per Pallet
 360

Listing Details

EAN Code 3800157629799

Commodity Code 9405403990

