

# **Product Specification Sheet**



### 6W VT-816 6W LED WALL LIGHT COLORCODE:3000K -WHITE BODY

Lumens 660

Beam Angle 350

Dimensions 110x54x97mm

Warm White SKU:8286







### **Technical Information**

Watts:	6
Lumens:	660
Beam Angle:	350
Unit Color:	White
Body Type:	Aluminium
Long life:	20,000 Hours
LED Chip Type:	SMD
IP Rating:	IP65

Dimmable: No

Warranty (Years): 2

PF: >0.5

CRI: >80

Operation Temperature: -20°C to +45°C

Input Power: AC:220-240V,50/60Hz

Sensor Compatibility: Yes

### **Features**



Designed for perfection - 360 Rotatable wall light



Available in different unit colors and color temperature options - Warm White and Day White

Excellent heat dissipation

Easy installation and Maintenance

Applications - Perfectly suitable for Indoor and Outdoor applications

Noto:



Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

## Packaging

#### **Unit Details**

 Gross Weight(GW) Kgs
 0.59

 Unit CBM
 0.00072

### Master Box Packaging

 Master Box Qty (Pcs Per Carton)
 20

 Qty Per Pallet
 1120

### Listing Details

 EAN Code
 3800157629805

 Commodity Code
 9405403990

