

Product Specification Sheet



Technical Information

Instant Start:	0-100% in lt1s
Watts:	12
Lumens:	1320
Beam Angle:	350
Unit Color:	White
Body Type:	Aluminium
Long life:	20,000 Hours
LED Chip Type:	SMD

Features

- Designed for perfection 360 Rotatable wall light
- High quality LED chips for a reliable lighting effect
- Available in different unit_colors and color temperature options Warm White and Day White
- Excellent heat dissipation
- Easy installation and Maintenance
- Applications Perfectly suitable for Indoor and Outdoor applications



Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details		Listing Details	
Gross Weight(GW) Kgs	1.03	EAN Code	3800157629867
Unit CBM	0.00042	Commodity Code	9405403990
Master Box Packaging			
Master Box Qty (Pcs Per Carton)	20		
Qty Per Pallet	600		

