



**12W**

VT-814 12W LED WALL LIGHT COLORCODE:3000K -GREY BODY

Lumens <b>1320</b>	Beam Angle <b>350</b>	Dimensions <b>230x54x97mm</b>
-----------------------	--------------------------	----------------------------------

Warm White  
SKU:8294

**2 YEARS**  
WARRANTY

**SENSOR**  
COMPATIBLE




## Technical Information

Instant Start:	0-100% in 11s	IP Rating:	IP65
Watts:	12	Dimmable:	No
Lumens:	1320	Warranty (Years):	2
Beam Angle:	350	PF:	>0.5
Unit Color:	Grey	CRI:	>80
Body Type:	Aluminium	Operation Temperature:	-20 to +45°C
Long life:	20,000 Hours	Input Power:	AC:110-240V,50/60Hz
LED Chip Type:	SMD	Sensor Compatibility:	Yes

## Features

- ✓ Designed for perfection - 360 Rotatable wall light
- ✓ High quality LED chips for a reliable lighting effect
- ✓ Available in different unit\_colors and color temperature options - Warm White and Day White
- ✓ Excellent heat dissipation
- ✓ Easy installation and Maintenance
- ✓ Applications - Perfectly suitable for Indoor and Outdoor applications

Note:  Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

# Packaging

## Unit Details

Gross Weight(GW) Kgs	1.03
Unit CBM	0.00042

## Listing Details

EAN Code	3800157629881
Commodity Code	9405403990

## Master Box Packaging

Master Box Qty (Pcs Per Carton)	20
Qty Per Pallet	600

READY STOCKS IN  
**UK & EU**



Dispatch within  
**24** Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER  
**70**  
COUNTRIES