

Product Specification Sheet



6W VT-826 6W LED WALL LIGHT COLORCODE:4000K -BLACK BODY

Lumens 660

Beam Angle 120

Dimensions 90x200x90mm

Day White SKU:8298







Technical Information

Watts:	6
Lumens:	660
Beam Angle:	120
Unit Color:	Black
Body Type:	Aluminium
Long life:	20,000 Hours
LED Chip Type:	SMD
IP Rating:	IP65

 Dimmable:
 No

 Warranty (Years):
 2

 PF:
 >0.5

 CRI:
 >80

 Operation Temperature:
 -20°C to +45°C

 Input Power:
 AC:220-240V,50/60Hz

 Sensor Compatibility:
 Yes

Features



High Quality Bridgelux chips for reliable operation and lifetime



Constructed to high quality aluminum for efficient heat dissipation

Cylindrical & Cubical fixtures in 3 colors to fit into range of archetictural structures

Elegant replacement for traditional up-down lighting

Application: Perfect for living rooms, pathways, balconies, facades etc





Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

 Gross Weight(GW) Kgs
 0.92

 Unit CBM
 0.00304175

Master Box Packaging

 Master Box Qty (Pcs Per Carton)
 20

 Qty Per Pallet
 480

Listing Details

 EAN Code
 3800157629928

 Commodity Code
 9405403990

