



**6W**

VT-836 6W LED WALL LIGHT COLORCODE:4000K -WHITE BODY

Lumens <b>660</b>	Beam Angle <b>90</b>	Dimensions <b>112x112x93mm</b>
----------------------	-------------------------	-----------------------------------

Day White  
SKU:8302

**2 YEARS**  
WARRANTY

**SENSOR**  
COMPATIBLE



## Technical Information

Instant Start:	0-100% in 11s
Watts:	6
Lumens:	660
Beam Angle:	90
Unit Color:	White
Body Type:	Aluminium
Long life:	20,000 Hours
LED Chip Type:	SMD

IP Rating:	IP65
Dimmable:	No
Warranty (Years):	2
PF:	>0.5
CRI:	>80
Operation Temperature:	-20 to +45°C
Input Power:	AC:220-240V,50/60Hz
Sensor Compatibility:	Yes

## Features

- ✓ High Quality Bridgelux chips for reliable operation and lifetime
- ✓ Get range of up-down beams with Adjustable beam angle to feel range of aesthetics
- ✓ Constructed to high quality aluminum for efficient heat dissipation
- ✓ Cylindrical & Cubical fixtures in 3 colors to fit into range of architectural structures
- ✓ Elegant replacement for traditional up-down lighting
- ✓ Application: Perfect for living rooms, pathways, balconies, facades etc

Note: 

Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

## Packaging

### Unit Details

Gross Weight(GW) Kgs	0.75
Unit CBM	0.001728

### Listing Details

EAN Code	3800157629966
Commodity Code	9405403990

### Master Box Packaging

Master Box Qty (Pcs Per Carton)	20
Qty Per Pallet	720

READY STOCKS IN  
**UK & EU**



Dispatch within  
**24** Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER

**70**

COUNTRIES