


Product Specification Sheet



6W VT-836 6W LED WALL LIGHT COLORCODE:3000K -BLACK BODY

Lumens 660

Beam Angle 90

Dimensions 112x112x93mm

Warm White SKU:8303







Technical Information


Watts:	6
Lumens:	660
Shape:	Round
Beam Angle:	90
Unit Color:	Black
Body Type:	Aluminium
Long life:	20,000 Hours
LED Chip Type:	SMD

IP Rating:	IP65
Dimmable:	No
Warranty (Years):	2
PF:	>0.5
CRI:	>80
Operation Temperature:	-20°C to +45°C
Input Power:	AC:220-240V,50/60Hz
Sensor Compatibility:	Yes

Features



High Quality Bridgelux chips for reliable operation and lifetime



Constructed to high quality aluminum for efficient heat dissipation

Cylindrical & Cubical fixtures in 3 colors to fit into range of archetictural structures

Elegant replacement for traditional up-down lighting

Application: Perfect for living rooms, pathways, balconies, facades etc





Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

 Gross Weight(GW) Kgs
 0.75

 Unit CBM
 0.001728

Master Box Packaging

 Master Box Qty (Pcs Per Carton)
 20

 Qty Per Pallet
 720

Listing Details

 EAN Code
 3800157629973

 Commodity Code
 9405403990

