

# **Product Specification Sheet**



# 6W VT-836 6W LED WALL LIGHT COLORCODE:4000K -GREY BODY

Lumens 660

Beam Angle 90

Dimensions 112x112x93mm

Day White SKU:8306







# **Technical Information**

Instant Start:	0-100% in lt1s
Watts:	6
Lumens:	660
Beam Angle:	90
Unit Color:	Grey
Body Type:	Aluminium
Long life:	20,000 Hours
LED Chip Type:	SMD

IP Rating:	IP65
Dimmable:	No
Warranty (Years):	2
PF:	>0.5
CRI:	>80
Operation Temperature:	-20 to +45°c
Input Power:	AC:220-240V,50/60Hz
Sensor Compatibility:	Yes

# **Features**



High Quality Bridgelux chips for reliable operation and lifetime



Constructed to high quality aluminum for efficient heat dissipation

Cylindrical & Cubical fixtures in 3 colors to fit into range of archetictural structures

Elegant replacement for traditional up-down lighting

Application: Perfect for living rooms, pathways, balconies, facades etc





Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

# Packaging

#### **Unit Details**

 Gross Weight(GW) Kgs
 0.75

 Unit CBM
 0.001728

# Master Box Packaging

 Master Box Qty (Pcs Per Carton)
 20

 Qty Per Pallet
 720

# Listing Details

 EAN Code
 3800157630009

 Commodity Code
 9405403990

