

# **Product Specification Sheet**



#### 10W

VT-811 10W LED WALL LIGHT COLORCODE:4000K -WHITE BODY

Lumens 1100

Beam Angle 360

Dimensions 300x215x60mm

Day White SKU:8308







## **Technical Information**

Watts:	10
Lumens:	1100
Beam Angle:	360
Unit Color:	White
Body Type:	Aluminium
Long life:	20,000 Hours
LED Chip Type:	SMD
IP Rating:	IP65

Dimmable: No

Warranty (Years): 2

PF: >0.45

CRI: >80

Operation Temperature: -20 to +45°c


Input Power: AC:110-240V,50/60Hz


Sensor Compatibility: Yes

## **Features**



Perfect choice of Interior lightingin for fabulous aesthetics and appeal





Portability and ease of maintenance

Available in different color options - Warm White and Day White

Applications - Residential, Building, Restaurants, Décor etc



Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

## Packaging

### **Unit Details**

 Gross Weight(GW) Kgs
 1.157

 Unit CBM
 0.004991

## Master Box Packaging

 Master Box Qty (Pcs Per Carton)
 20

 Qty Per Pallet
 240

## Listing Details

EAN Code 3800157630023

Commodity Code 9405403990

