

Product Specification Sheet



10W VT-811 10W LED WALL LIGHT COLORCODE:4000K -BLACK BODY

Lumens 1100

Beam Angle 360

Dimensions 300x215x60mm

Day White SKU:8310







Technical Information

Watts:	10
Lumens:	1100
Beam Angle:	360
Unit Color:	Black
Body Type:	Aluminium
Long life:	20,000 Hours
LED Chip Type:	SMD
IP Rating:	IP65

 Dimmable:
 No

 Warranty (Years):
 2

 PF:
 >0.45

 CRI:
 >80

 Operation Temperature:
 -20 to +45°c

 Input Power:
 AC:110-240V,50/60Hz


 Sensor Compatibility:
 Yes

Features



Perfect choice of Interior lightingin for fabulous aesthetics and appeal





Portability and ease of maintenance

Available in different color options - Warm White and Day White

Applications - Residential, Building, Restaurants, Décor etc





Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

 Gross Weight(GW) Kgs
 1.157

 Unit CBM
 0.004991

Master Box Packaging

 Master Box Qty (Pcs Per Carton)
 20

 Qty Per Pallet
 240

Listing Details

 EAN Code
 3800157630047

 Commodity Code
 9405403990

