

**3W**

VT-803 3W-WALL LAMP WITH BRIDGELUX CHIP COLORCODE:4000K  
 WHITE BODY

Lumens <b>300</b>	Beam Angle <b>120</b>	Dimensions <b>220x80x200mm</b>
----------------------	--------------------------	-----------------------------------

Day White  
 SKU:8345




### Technical Information

Watts:	3	Dimmable:	No
Lumens:	300	Warranty (Years):	2
On/Off Cycles:	15000	PF:	>0.5
Beam Angle:	120	CRI:	>80
Unit Color:	White	Operation Temperature:	-20 to +45°C
Body Type:	Iron	Input Power:	AC:110-240V,50/60Hz
Long life:	30,000 Hours	Sensor Compatibility:	Yes
IP Rating:	IP20		

### Features

- ✓ Modern Wall lights available in sleek and stylish designs.
- ✓ Excellent heat dissipation
- ✓ Available in different color options - Warm White and Day White
- ✓ Easy installation and Maintenance
- ✓ Application: Perfect for halls, pathways, Bedroom, Kitchen etc

Note:  Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

## Packaging

### Unit Details

Gross Weight(GW) Kgs	0.78
Unit CBM	0.004232

### Listing Details

EAN Code	3800157633017
Commodity Code	9405403990

### Master Box Packaging

Master Box Qty (Pcs Per Carton)	20
Qty Per Pallet	160

READY STOCKS IN  
**UK & EU**



Dispatch within  
**24** Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER

**70**

COUNTRIES