

Product Specification Sheet



VT-837 WALL LAMP(1*E27) MATT WHITE-CLEAR GLASS

Dimensions 113x236x113mm

SKU:8518





Technical Information

Holder Type: E27

Rated Load: Max 60W

Unit Color: Matt White

Body Type: Aluminium + Clear Glass

IP Rating: IP44

Dimmable: No
Warranty (Years): 3
Operation Temperature: -20? to 45?
Input Power: AC:220-240V, 50/60Hz

Features

- Traditional Garden Lamps designed to fit the Modern day requirements
- Available in different designs, shapes and sizes
- ✓ Waterproof Lamps available in series of IP rating from IP44 to IP54
- Easy to Install and low Maintenance
- Suitable with E27 base lights(Fitting only Light not included)
- ✓ Application: Suitable for Garden, Floor, Ceiling etc

Packaging

Unit Details

 Gross Weight(GW) Kgs
 1.4

 Unit CBM
 0.0036

Master Box Packaging

 Master Box Qty (Pcs Per Carton)
 10

 Qty Per Pallet
 240

Listing Details

 EAN Code
 3800157637442

 Commodity Code
 9405109890

